


Fabrication Guide



FOME-COR® DISPA® POLAR™ SWEDBOARD® SINTRA® GATOR® LUMEX® G DIBOND®

Quick reference sheet for possible fabrication methods for 3A products

	Mounting	Repositioning Vinyl	Digital Printing	Screen Printing	Painting	Knife Cutting	Saw Cutting	Routing	Die Cutting/ Punching	Embossing	Forming	Creasing
\$ FOME-COR FOUNDATION (Acid-Free)	◇ ⁰					◇			◇	◇		
FOME-COR	◇		◇	◇	◇ ³	◇			◇	◇		
FOME-COR w/ ENCORE Technology	◇		◇	◇	◇ ³	◇			◇			
FOME-COR SIRIUS			◇			◇			◇	◇		
FOME-COR SINGLESTEP (Heat-Activated)	◇					◇			◇	◇		
FOME-COR CANVAS			◇	◇	◇	◇			◇	◇		
FOME-COR JETMOUNT	◇		◇	◇	◇ ³	◇	◇	◇	◇	◇		
FOME-COR QUICKSTIK (Self-Adhesive)	◇					◇			◇	◇		
DISPA	◇		◇	◇	◇	◇		◇	◇		◇	◇
DISPA SIRIUS			◇			◇		◇	◇		◇	◇
NEW! POLAR	◇		◇	◇	◇	◇		◇			◇	
\$\$ SINTRA CONSTRUCT	◇ ¹	◇			◇		◇	◇	◇ ⁵		◇	
SINTRA VERS	◇ ¹	◇	◇	◇	◇	◇ ⁴	◇	◇	◇ ⁵		◇	
SINTRA	◇ ¹	◇	◇	◇	◇	◇ ⁴	◇	◇	◇ ⁵		◇	
SINTRA ECLIPSE	◇ ¹	◇	◇	◇	◇	◇ ⁴	◇	◇	◇ ⁵		◇	
NEW! SINTRA XT	◇ ¹	◇	◇	◇	◇		◇	◇	◇		◇	
GATORBLANKS	◇				◇	◇	◇	◇				
GATORPLAST	◇	◇	◇	◇	◇ ³	◇	◇	◇	◇ ⁵			
GATORFOAM	◇		◇	◇ ²	◇ ³		◇	◇				
GATORFOAM PRO	◇		◇	◇ ²	◇ ³		◇	◇				
GATORFOAM EXTERIOR	◇		◇	◇ ²	◇ ³		◇	◇				
GATORFOAM SELF-ADHESIVE	◇	◇					◇	◇				
LUMEX G	◇	◇	◇	◇	◇		◇	◇	◇		◇	
NEW! SWEDBOARD FIBRE	◇		◇	◇	◇	◇		◇			◇	
\$\$\$ DIBOND	◇ ¹	◇	◇	◇	◇		◇	◇	◇ ⁶		◇	

Trialing is recommended to ensure suitability for the proposed fabrication before full-scale commercialization.

- 0 Archival conservation mounting
- 1 Cold mounting techniques only
- 2 Face priming will provide better results
- 3 Do not expose polystyrene foam to solvent-based paints
- 4 1-3mm may be cut with a knife or blade
- 5 May be die cut in gauges up to 5mm or 3/16"
- 6 Punch press die set is required